



ColorGraz MX4 Powercore

BCS559 9 RGBW L305

RGBW - 9° x 9° - 305 mm

High-output luminaire for high-intensity multi-story façade and surface illumination at minimal setback; RGBW and RGBA options provide an expanded color palette and white light capability in one fixture.

Product data

General Information	
Lamp family code	LED-HB [LED High Brightness]
Light source color	RGBW
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	PC [Polycarbonate bowl/cover]
Luminaire light beam spread	9° x 9°
Protection class IEC	Safety class I (I)
CE mark	CE mark
UL mark	UL and cUL mark
Operating and Electrical	
Input Voltage	100 to 277 V
Input Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	305 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Vibration Standard	Complies with ANSI C136.31, 3G
Vibration Rating	Complies with ANSI C136.31, 3G
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	655 lm
Initial LED luminaire efficacy	36.3 lm/W
Initial input power	18.5 W

ColorGraz e MX4 Powercore

Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25°C Reported	75000
Lumen Maintenance 50% at 50°C Reported	70000
Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	70000
Lumen Maintenance 70% at 50°C Calculated	100000
Lumen Maintenance 70% at 50°C Reported	65000

Application Conditions	
Ambient temperature range	-40 to +50 °C

Product Data	
Full product code	871829161977299

Order product name	BCS559 9 RGBW L305
EAN/UPC - Product	8718291619772
Order code	910503704681
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	910503704681
Net Weight (Piece)	1.200 kg

Dimensional drawing

