



ColorGraze MX4 Powercore



ColorGraze MX4 Powercore, RGBW, 15° x 30° Beam Angle, 610 mm (2 ft)

ColorGraze MX4 Powercore, RGBW, 15° x 30° Beam Angle, 610 mm (2 ft)

High-output luminaire for high-intensity multi-story façade and surface illumination at minimal setback; RGBW and RGBA options provide an expanded color palette and white light capability in one fixture.

Product data

General information	
Lamp family code	LED-HB [LED High Brightness]
Light source colour	RGBW
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	PC [Polycarbonate bowl/cover]
Luminaire light beam spread	15° x 30°
Protection class IEC	Safety class I
CE mark	CE mark
UL mark	UL and cUL mark
Operating and electrical	
Input Voltage	100 to 277 V
Input frequency	50 to 60 Hz

Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Extruded aluminium
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	610 mm
Approval and application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK10 [20 J vandal-resistant]
Vibration standard	Complies with ANSI C136.31, 3G
Vibration rating	Complies with ANSI C136.31, 3G


ColorGrazе MX4 Powercore

887823	
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	1244 lm
Initial LED luminaire efficacy	34.4 lm/W
Initial input power	37 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Reported	75000
Lumen Maintenance 50% at 50 °C Reported	70000
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	70000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	65000
Application conditions	
Ambient temperature range	-40 to +50 °C

Product data	
Full product code	871829161984099
Order product name	BCS559 15x30 RGBW L609
EAN/UPC – product	8718291619840
Order code	423-000001-07
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	910503704688
Net Weight (Piece)	0.825 kg
Commercial Code	423-000001-07
Catalogue number description	ColorGrazе MX4 Powercore, RGBW, 15° x 30° Beam Angle, 610 mm (2 ft)



Dimensional drawing



BCS559 15x30 RGBW L609

