



ColorGraze MX4 Powercore

BCS559 60x30 RGBW L914

RGBW - 60° x 30° - 914 mm

High-output luminaire for high-intensity multi-story façade and surface illumination at minimal setback; RGBW and RGBA options provide an expanded color palette and white light capability in one fixture.

Product data

General Information	
Lamp family code	LED-HB [LED High Brightness]
Light source color	RGBW
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	PC [Polycarbonate bowl/cover]
Luminaire light beam spread	60° x 30°
Protection class IEC	Safety class I (I)
CE mark	CE mark
UL mark	UL and cUL mark
FCC mark	FCC Class A
Operating and Electrical	
Input Voltage	100 to 277 V
Input Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	914 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	1902 lm
Initial LED luminaire efficacy	34.8 lm/W
Initial input power	55.5 W
Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25°C Reported	75000
Lumen Maintenance 50% at 50°C Reported	70000
Lumen Maintenance 70% at 25°C Calculated	100000

ColorGraz e MX4 Powercore

Lumen Maintenance 70% at 25°C Reported	70000
Lumen Maintenance 70% at 50°C Calculated	100000
Lumen Maintenance 70% at 50°C Reported	65000

Application Conditions

Ambient temperature range	-40 to +122 °F
---------------------------	----------------

Product Data

Full product code	871829161961100
Order product name	BCS559 60x30 RGBW L914

EAN/UPC - Product	8718291619611
Order code	910503704695
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910503704695
Net Weight (Piece)	3.800 kg

Dimensional drawing

