



# ColorGraze MX4 Powercore



## ColorGraze MX4 Powercore, RGBA, 60° x 30° Beam Angle, 305 mm (1 ft)

ColorGraze MX4 Powercore, RGBA, - 60° x 30° Beam Angle, 305 mm (1 ft)

High-output luminaire for high-intensity multi-story façade and surface illumination at minimal setback; RGBW and RGBA options provide an expanded color palette and white light capability in one fixture.

### Product data

General information	
Lamp family code	LED-HB [ LED High Brightness]
Light source colour	RGBA
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	PC [ Polycarbonate bowl/cover]
Luminaire light beam spread	60° x 30°
Protection class IEC	Safety class I
CE mark	CE mark
UL mark	UL and cUL mark

Operating and electrical	
Input Voltage	100 to 277 V
Input frequency	50 to 60 Hz

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Housing material	Extruded aluminium
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	305 mm

Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Vibration standard	Complies with ANSI C136.31, 3G
FCC mark	FCC Class A

# ColorGrazе MX4 Powercore

Vibration rating	Complies with ANSI C136.31, 3G
	887719

## Initial performance (IEC compliant)

Initial luminous flux (system flux)	561 lm
Initial LED luminaire efficacy	28 lm/W
Initial input power	18.5 W

## Over time performance (IEC compliant)

Lumen Maintenance 50% at 25 °C Reported	7500
Lumen Maintenance 50% at 50 °C Reported	70000
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	70000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	65000

## Application conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Product data

Full product code	871829161991899
Order product name	BCS559 60x30 RGBA L305
EAN/UPC – product	8718291619918
Order code	423-000002-04
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	910503704706
Net Weight (Piece)	1.200 kg
Commercial Code	423-000002-04
Catalogue number description	ColorGrazе MX4 Powercore, RGBA, 60° x 30° Beam Angle, 305 mm (1 ft)



## Dimensional drawing



BCS559 60x30 RGBA L305

