



# ColorGraze MX4 Powercore



## ColorGraze MX4 Powercore, RGBA, 60° x 30° Beam Angle, 305 mm (1 ft)

ColorGraze MX4 Powercore, RGBA, – 60° x 30° Beam Angle, 305 mm (1 ft)

ColorGraze MX4 Powercore is a high-performance, exterior linear luminaire designed to highlight architectural features ranging from surface textures and molding details to archways and windows. Graze RGBW luminaires add a separate white LED creating better-quality whites compared to RGB. Graze RGBA luminaires add a separate amber LED which expands the available range of colors to include warmer tones such as rich gold, yellow, and orange shades. Multiple fixture lengths, and beam angles support a large range of façade or surface illumination applications. Low-profile housing, connectorized cabling, a universal power input range, and direct line voltage operation make Graze luminaires easy to install and operate.

### Product data

General information		UL mark	
Lamp family code	LED-HB [ LED High Brightness]	UL and cUL mark	
Light source color	RGBA	Operating and electrical	
Light source replaceable	No	Input Voltage	100 to 277 V
Driver included	Yes	Input Frequency	50 to 60 Hz
Optical cover/lens type	Polycarbonate bowl/cover	Controls and dimming	
Luminaire light beam spread	60° x 30°	Dimmable	Yes
Protection class IEC	Safety class I		
CE mark	CE mark		

ColorGrazе MX4 Powercore

Mechanical and housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	305 mm

Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Vibration Standard	Complies with ANSI C136.31, 3G
Corrosion Resistance	Complies with ASTM B117 standard with special order. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
FCC mark	FCC Class A
Vibration Rating	Complies with ANSI C136.31, 3G
EPREL Registration Number	887719

Initial performance (IEC compliant)	
Initial luminous flux (system flux)	561 lm
Initial LED luminaire efficacy	28 lm/W
Initial input power	18.5 W

Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C Reported	7500
Lumen Maintenance 50% at 50°C Reported	70000


Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	70000
Lumen Maintenance 70% at 50°C Calculated	100000
Lumen Maintenance 70% at 50°C Reported	65000

Application conditions	
Ambient temperature range	-40 to +50 °C

Product data	
Full product code	871829161991899
Order product name	BCS559 60x30 RGBA L305
EAN/UPC - Product	8718291619918
Order code	423-000002-04
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	910503704706
Net Weight (Piece)	1.200 kg
Catalog Number	423-000002-04
Catalog Number Description	ColorGrazе MX4 Powercore, RGBA, 60° x 30° Beam Angle, 305 mm (1 ft)



Dimensional drawing



BCS559 60x30 RGBA L305

## ColorGrazе MX4 Powercore

