



ColorGraz MX4 Powercore



ColorGraz MX4 Powercore, RGBA, 10° x 60° Beam Angle, 1219 mm (4 ft)

ColorGraz MX4 Powercore, RGBA, 10° x 60° Beam Angle, 1219 mm (4 ft)

High-output luminaire for high-intensity multi-story façade and surface illumination at minimal setback; RGBW and RGBA options provide an expanded color palette and white light capability in one fixture.

Product data

General information	
Lamp family code	LED-HB [LED High Brightness]
Light source colour	RGBA
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	PC [Polycarbonate bowl/cover]
Luminaire light beam spread	10° x 60°
Protection class IEC	Safety class I
CE mark	CE mark
UL mark	UL mark
Operating and electrical	
Input Voltage	100 to 277 V
Input frequency	50 to 60 Hz

Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Extruded aluminium
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	1219 mm
Approval and application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK10 [20 J vandal-resistant]
Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the

ColorGrazе MX4 Powercore

	standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
FCC mark	FCC Class A
Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
	887732

Initial performance (IEC compliant)

Initial luminous flux (system flux)	2172 lm
Initial LED luminaire efficacy	27 lm/W
Initial input power	74 W

Over time performance (IEC compliant)

Lumen Maintenance 50% at 25 °C	75000
Reported	
Lumen Maintenance 50% at 50 °C	70000
Reported	
Lumen Maintenance 70% at 25 °C	100000
Calculated	
Lumen Maintenance 70% at 25 °C	70000
Reported	

Lumen Maintenance 70% at 50 °C	100000
Calculated	
Lumen Maintenance 70% at 50 °C	65000
Reported	

Application conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data

Full product code	871829161973400
Order product name	BCS559 10x60 RGBA L1219
EAN/UPC – product	8718291619734
Order code	423-000002-16
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503704718
Net Weight (Piece)	4.700 kg
Commercial Code	423-000002-16
Catalogue number description	ColorGrazе MX4 Powercore, RGBA, 10° x 60° Beam Angle, 1219 mm (4 ft)



Dimensional drawing

