



# ColorGraz MX4 Powercore

## ColorGraz MX4 Powercore, RGBA, 15° x 30° Beam Angle, 1219 mm (4 ft)

ColorGraz MX4 Powercore, RGBA, 15° x 30° Beam Angle, 1219 mm (4 ft)

High-output luminaire for high-intensity multi-story façade and surface illumination at minimal setback; RGBW and RGBA options provide an expanded color palette and white light capability in one fixture.

### Product data

General information		Controls and dimming	
Lamp family code	LED-HB [ LED High Brightness]	Dimmable	Yes
Lamp colour code	RGBA		
Light source replaceable	No	Mechanical and housing	
Driver included	Yes	Housing material	Aluminum extruded
Optical cover/lens type	PC [ Polycarbonate bowl/cover]	Optic material	Polycarbonate
Luminaire light beam spread	15° x 30°	Optical cover/lens material	Polycarbonate
Protection class IEC	Safety class I (I)	Length	1219 mm
CE mark	CE mark	Approval and application	
UL mark	UL and cUL mark	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Operating and electrical		Energy Efficiency Class	G
Input Voltage	100 to 277 V	Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Input frequency	50 to 60 Hz	Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the

ColorGrazе MX4 Powercore

	standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
FCC mark	FCC Class A
Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
	887733

Initial performance (IEC compliant)

Initial luminous flux (system flux)	2220 lm
Initial LED luminaire efficacy	30.9 lm/W
Initial input power	74 W

Over time performance (IEC compliant)

Lumen Maintenance 50% at 25 °C	75000
Reported	
Lumen Maintenance 50% at 50 °C	70000
Reported	
Lumen Maintenance 70% at 25 °C	100000
Calculated	
Lumen Maintenance 70% at 25 °C	70000
Reported	

Lumen Maintenance 70% at 50 °C	100000
Calculated	
Lumen Maintenance 70% at 50 °C	65000
Reported	

Application conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data

Full product code	871829161974100
Order product name	BCS559 15x30 RGBA L1219
EAN/UPC – product	8718291619741
Order code	423-000002-17
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503704719
Net Weight (Piece)	4.700 kg
Commercial Code	423-000002-17
Commercial Code	ColorGrazе MX4 Powercore, RGBA, 15° x 30° Beam Angle, 1219 mm (4 ft)



Dimensional drawing

