



# LuxSpace, recessed

## DN570B LED20S/830 PSD-VLC-E C ELP3 WH

LuxSpace, recessed, 22 W, 2200 lm, 3000 K, DALI, Frosted

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is. For office applications LuxSpace supports health and wellbeing having dedicated Tunable White products and lighting controls.

### Product data


| General Information      |  | Value ladder                       | Specification                               |
|--------------------------|--|------------------------------------|---|
| Lamp family code         | LED20S [LED Module, system flux 2000 lm]   | CE mark                            | Yes   |
| Cap-Base                 | - [-]  | Warranty period                    | 5 years                                     |
| Light source replaceable | No   | Flammability mark                  | For mounting on normally flammable surfaces |
| Number of gear units     | 1 unit   | ENEC mark                          | -   |
| Gear                     | -  | Glow-wire test                     | Temperature 850 °C, duration 5 s            |
| Driver included          | Yes  | EU RoHS compliant                  | No  |
| Remarks                  | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. |                                    |   |
| Product family code      | DN570B [LUXSPACE 2 COMPACT LOW HEIGHT]   | Light Technical                    |   |
| Lighting Technology      | LED  | Luminous Flux                      | 2,200 lm                                    |
|                          |  | Correlated Color Temperature (Nom) | 3000 K                                      |
|                          |  | Luminous Efficacy (rated) (Nom)    | 100 lm/W                                    |
|                          |  | Color rendering index (CRI)        | >80   |
|                          |  | Light source color                 | 830 warm white                              |
|                          |  | Optic type                         | High-gloss mirror                           |
|                          |  | Luminaire light beam spread        | 80°   |

LuxSpace, recessed

|  |  |
|--|--|
| Unified glare rating CEN                 | 22   |
| Operating and Electrical                 |  |
| Input Voltage                            | 220 to 240 V   |
| Line Frequency                           | 50 to 60 Hz  |
| Inrush current                           | 20.4 A   |
| Inrush time                              | 0.195 ms   |
| Power Consumption                        | 22 W   |
| Power Factor (Fraction)                  | 0.9  |
| Connection                               | Push-in connector and pull relief                              |
| Cable                                    | -  |
| Number of products on MCB of 16 A type B | 24   |
| Temperature                              |  |
| Ambient temperature range                | +10 to +25 °C  |
| Controls and Dimming                     |  |
| Dimmable                                 | Yes  |
| Driver/power unit/transformer            | Power supply unit with DALI interface, DC compatible, external |
| Control interface                        | DALI   |
| Constant light output                    | No   |
| Mechanical and Housing                   |  |
| Housing Material                         | Aluminum die cast  |
| Reflector material                       | Polycarbonate aluminum coated                                  |
| Optic material                           | Polycarbonate  |
| Optical cover material                   | Polycarbonate  |
| Fixation material                        | Steel  |
| Housing Color                            | White RAL 9003   |
| Optical cover finish                     | Frosted  |
| Overall height                           | 96.5 mm  |
| Overall diameter                         | 214 mm   |

|   |                                       |
|---|---------------------------------------|
| Approval and Application                                |                                       |
| Ingress protection code                                 | IP20 [Finger-protected]               |
| Mech. impact protection code                            | IK02 [0.2 J standard]                 |
| Protection class IEC                                    | Safety class II                       |
| Initial Performance (IEC Compliant)                     |                                       |
| Luminous flux tolerance                                 | +/-10%                                |
| Initial chromaticity                                    | (0.43, 0.40) SDCM <3                  |
| Power consumption tolerance                             | +/-10%                                |
| Over Time Performance (IEC Compliant)                   |                                       |
| Control gear failure rate at median useful life 50000 h | 5 %                                   |
| Lumen maintenance at median useful life* 50000 h        | L90                                   |
| Lumen maintenance at median useful life* 100000 h       | L80                                   |
| Application Conditions                                  |                                       |
| Performance ambient temperature Tq                      | 25 °C                                 |
| Maximum dim level                                       | 1% (no dimming in emergency mode)     |
| Suitable for random switching                           | Yes                                   |
| Product Data  |                                       |
| Order product name                                      | DN570B LED20S/830 PSD-VLC-E C ELP3 WH |
| Full product name                                       | DN570B LED20S/830 PSD-VLC-E C ELP3 WH |
| Full product code                                       | 871829194378500                       |
| Order code  | 910503706691                          |
| Material Nr. (12NC)                                     | 910503706691                          |
| Numerator - Quantity Per Pack                           | 1                                     |
| EAN/UPC - Product/Case                                  | 8718291943785                         |
| Numerator - Packs per outer box                         | 1                                     |
| EAN/UPC - Case  | 8718291943785                         |

Dimensional drawing



LuxSpace, recessed

