



LuxSpace, recessed

DN571B LED20S/840 PSED-VLC-E C ELP3 WH

LUXSPACE 2 COMPACT DEEP - LED Module, system flux 2000 lm - 840 neutral white - Power supply unit with DALI interface external, DC compatible for central emergency lighting - High-gloss mirror - Emergency lighting 3 hours duration Pro version - Push-in connector and pull relief - White

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

Product data

General information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]	Luminaire light beam spread	70°
Light source colour	840 neutral white	Emergency lighting	Emergency lighting 3 hours duration Pro version
Cap base	- [-]	Control interface	DALI
Light source replaceable	No	Connection	Push-in connector and pull relief
Number of gear units	1 unit	Cable	-
Gear	-	Protection class IEC	Safety class II
Driver/power unit/transformer	PSED-E [Power supply unit with DALI interface external, DC compatible for central emergency lighting]	Glow-wire test	Temperature 850 °C, duration 5 s
Driver included	Yes	Flammability mark	F [For mounting on normally flammable surfaces]
Optic type	C [High-gloss mirror]	CE mark	CE mark
		ENEC mark	-

LuxSpace, recessed

UL mark	No
Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB	24
RoHS mark	-
Product Family Code	DN571B [LUXSPACE 2 COMPACT DEEP]
Unified glare rating CEN	19

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Aluminium die-cast
Reflector material	Polycarbonate aluminium coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall height	119 mm
Overall diameter	214 mm
Colour	White

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	2100 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	121 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	>80
Initial chromaticity	(0.38, 0.37) SDCM <3
Initial input power	17.4 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90


Application Conditions

Ambient temperature range	+10 to +25 °C
Performance ambient temperature Tq	25 °C

Product Data

Full product code	871829194384600
Order product name	DN571B LED20S/840 PSED-VLC-E C ELP3 WH
EAN/UPC – product	8718291943846
Order code	94384600
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910503706697
Net weight (piece)	1.680 kg

Dimensional drawing



LuxSpace gen2 DN570B-DN572B

