



UrbanScene

CGP705 CDM-TD150W/830 EB II A FG CO GR

UrbanScene Mid, MASTERColour CDM-TD, 150 W, Electronic, Asymmetrical, Flat glass

UrbanScene is a range of complete lighting solutions comprising five highly distinctive urban lighting luminaires, plus dedicated masts and brackets. Their flexibility, coherent design and outstanding optical performance allow them to fulfill all main applications – street lighting, area lighting, illumination and image projection. UrbanScene’s energy-saving features (high-efficiency lamps, electronic gear) enable municipal authorities to adopt a sustainable approach to urban lighting. Designed to be unobtrusive, night-preserving and fully recyclable, UrbanScene has an elegant daytime appearance. Smart brackets allow total flexibility in aiming, while preserving the overall appearance of the light point. The UrbanScene range consists of small and medium-sized luminaires, as well as gobo projector, LED and indirect versions.

Product data

General Information	
Lamp family code	CDM-TD [MASTERColour CDM-TD]
Gear	EB [Electronic]
Photocell	-
Product family code	CGP705 [UrbanScene Mid]
Embedded control	-
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Light source color	830 warm white
Optical cover type	Flat glass

Optic type outdoor	Asymmetrical
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	150 W
Cable	-
Mechanical and Housing	
Housing Color	Grey
Parts color	Cover painted

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

Product Data

Order product name	CGP705 CDM-TD150W/830 EB II A FG CO GR
Full product name	CGP705 CDM-TD150W/830 EB II A FG CO GR
Full product code	871794395447600

Order code	910503720518
Material Nr. (12NC)	910503720518
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943954476
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943954476

Dimensional drawing

