



# TCS165

## TCS165 4XTL5-14W/840 HF C6 PIP

4, TL5, 14 W, 840 neutral white, Electronic high-frequency, High-gloss optic double parabolic closed

Designed to meet the need for energy-efficient lighting, the TCS165 luminaire incorporates Philips TL5 technology, which means it saves on energy and is ideal for replacing outdated facilities. With its innovative design and dedicated optics, the TCS165 range can be applied as general lighting in a wide variety of applications including offices, corridors, schools, and shops (supermarkets, DIY). Used in combination with electronic ballasts and Philips TL5 lamps, it provides substantial energy savings.

### Product data

<b>General Information</b>		<b>Power Consumption</b>	
Lamp family code	TL5 [TL5]	14 W	
Gear	HF [Electronic high-frequency]	<b>Approval and Application</b>	
CE mark	Yes	Ingress protection code	IP20 [Finger-protected]
Flammability mark	For mounting on normally flammable surfaces	Mech. impact protection code	IK02 [0.2 J standard]
ENEC mark	-	Protection class IEC	Safety class I
<b>Light Technical</b>		<b>Application Conditions</b>	
Number of light sources	4	Suitable for random switching	Not applicable
Light source color	840 neutral white	<b>Product Data</b>	
Optic type	High-gloss optic double parabolic closed	Order product name	TCS165 4XTL5-14W/840 HF C6 PIP
<b>Operating and Electrical</b>		Full product name	TCS165 4XTL5-14W/840 HF C6 PIP
Input Voltage	220 to 240 V	Full product code	871869606933200
Line Frequency	50 to 60 Hz	Order code	910503910079
		Material Nr. (12NC)	910503910079

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696069332
Numerator - Packs per outer box	1

EAN/UPC - Case	8718696069332
----------------	---------------

Dimensional drawing

