



TCS165

TCS165 2XTL5-28W/840 HF C6 PIP

2, TL5, 28 W, 840 neutral white, Electronic high-frequency, High-gloss optic double parabolic closed

Designed to meet the need for energy-efficient lighting, the TCS165 luminaire incorporates Philips TL5 technology, which means it saves on energy and is ideal for replacing outdated facilities. With its innovative design and dedicated optics, the TCS165 range can be applied as general lighting in a wide variety of applications including offices, corridors, schools, and shops (supermarkets, DIY). Used in combination with electronic ballasts and Philips TL5 lamps, it provides substantial energy savings.

Product data

General Information		Power Consumption	
Lamp family code	TL5 [TL5]		28 W
Gear	HF [Electronic high-frequency]	Approval and Application	
CE mark	Yes	Ingress protection code	IP20 [Finger-protected]
Flammability mark	For mounting on normally flammable surfaces	Mech. impact protection code	IK02 [0.2 J standard]
ENEC mark	-	Protection class IEC	Safety class I
Light Technical		Application Conditions	
Number of light sources	2	Suitable for random switching	Not applicable
Light source color	840 neutral white	Product Data	
Optic type	High-gloss optic double parabolic closed	Order product name	TCS165 2XTL5-28W/840 HF C6 PIP
Operating and Electrical		Full product name	TCS165 2XTL5-28W/840 HF C6 PIP
Input Voltage	220 to 240 V	Full product code	871869606934900
Line Frequency	50 to 60 Hz	Order code	06934900
		Material Nr. (12NC)	910503910080

TCS165

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696069349
Numerator - Packs per outer box	1

EAN/UPC - Case	8718696069349
----------------	---------------

Dimensional drawing

