



# CoreLine SlimDownlight

## DN135C LED10S/840 PSU II WH

LED Module, system flux 1000 lm, 840 neutral white, Power supply unit (On/Off), Safety class II, White

CoreLine slimdownlight delivers on the CoreLine promise of innovative, easy-to-use and high-quality indoor LED downlights. The CoreLine slim downlight is an innovative range of recessed and surface-mounted luminaires. It is designed to provide uniform lighting across multiple application areas. With instant energy-savings and a longer lifetime, this is an environmentally friendly and cost-saving solution. Its MultiColorTemp feature offers a choice of two colour temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes in stock. Simple and easy installation means that our slim downlight fits the same size cut-out, while the minimal built-in depth of 34 mm makes this product an ideal space-saving solution, especially for projects with limited fitting space. InterAct Ready option with integrated wireless communications in this family is available, to be used with InterAct gateways, sensors and software.

### Product data

General Information		luminares – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Lamp family code	LED10S [LED Module, system flux 1000 lm]	
Light source replaceable	No	
Number of gear units	Unit	
Gear	-	
Driver included	Yes	Lighting Technology
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based	
		Value ladder
		Performance

# CoreLine SlimDownlight

CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

## Light Technical

Luminous Flux	1,000 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	77 lm/W
Colour rendering index (CRI)	>80
Beam angle of light source	- degree(s)
Light source colour	840 neutral white
Optic type	-
Optical cover type	Opal
Luminaire light beam spread	135°
Unified Glare Rating (CEN)	28

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	3.4 A
Inrush time	29 ms
Power Consumption	13 W
Power Factor (Fraction)	0.9
Connection	Push-in connector with 2 poles and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

## Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

## Mechanical and Housing

Housing material	Aluminium
------------------	-----------

Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Housing Colour	White
Optical cover/lens finish	Frosted
Overall height	50 mm
Overall diameter	165 mm

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* L70 50,000 h	

## Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

## Product Data

Order product name	DN135C LED10S/840 PSU II WH
Full product name	DN135C LED10S/840 PSU II WH
Full EOC	871869607047599
Order code	07047599
Material no. (12 NC)	910503910115
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696070475
Numerator – packs per outer box	12
EAN/UPC – Case	8718696070550

## CoreLine SlimDownlight

### Dimensional drawing

