



# CoreLine Recessed Spot

## RS140B LED6-60-/840 PSR PI6 WH

CoreLine Recessed Spot, 10 W, 650 lm, 4000 K, Analog, Beam angle 60°, White

CoreLine Recessed Spot delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. CoreLine Recessed Spot is a recessed spot range designed to replace halogen-based luminaires. Its halogen-like look and attractive price make it easier for customers to make the switch to LED. This product provides a natural lighting effect for accent lighting applications, as well as instant energy savings and much longer lifetime – an environmentally friendly solution. With the push-in connectors, installation is fast and straightforward.

### Product data

General Information		Value ladder	Performance
Lamp family code	LED6S [LED Module, system flux 600 lm]	CE mark	Yes
Cap-Base	- [-]	Warranty period	3 years + 2 years upon registration
Light source replaceable	No	Flammability mark	For mounting on normally flammable surfaces
Number of gear units	1 unit	ENEC mark	-
Driver included	Yes	Glow-wire test	Temperature 650 °C, duration 5 s
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Lighting Technology	LED	Light Technical	
		Luminous Flux	650 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	65 lm/W
		Color rendering index (CRI)	85

## CoreLine Recessed Spot

Number of light sources	1
Beam angle of light source	60 degree(s)
Light source color	840 neutral white
Optic type	Beam angle 60°
Optical cover type	Polycarbonate bowl/cover clear
Luminaire light beam spread	60°

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	7 A
Inrush time	500 ms
Power Consumption	10 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type B	-

### Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Analog
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White
Optical cover finish	Clear
Overall height	60 mm

Overall diameter	95 mm
------------------	-------

### Approval and Application

Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70


### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

### Product Data

Order product name	RS140B LED6-60-/840 PSR PI6 WH
Full product name	RS140B LED6-60-/840 PSR PI6 WH
Full product code	871869607126799
Order code	910503910147
Material Nr. (12NC)	910503910147
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696071267
Numerator - Packs per outer box	18
EAN/UPC - Case	8718696071311

## Dimensional drawing



## CoreLine Recessed Spot

