



# ClearAccent

## RS060B LED5-36-/830 PSR II WH

ClearAccent, 6 W, 500 lm, 3000 K, Analog, Symmetrical, White

ClearAccent is an entry-level recessed spot range designed to replace halogen-based luminaires. Its attractive price and high lumen per watt ratio make the decision to switch to LED an easy one. The luminaire's compact design, with built-in driver, is suitable for a wide variety of applications. The dimensions of the fixation hole meet the old halogen-based standard of 68 mm, which makes retrofitting possible. Thanks to the screw-in connectors, installation is easy and safe. These spotlights are fully IC compliant.

### Product data

General Information		Operating and Electrical	
Light source replaceable	No	Input Voltage	220-240 V
Gear	-	Line Frequency	50 to 60 Hz
Lighting Technology	LED	Input Frequency	50 to 60 Hz
Value ladder	Value	Power Consumption	6 W
CE mark	CE mark	Power Factor (Fraction)	0.9
Warranty period	3 years	Connection	Screw connection block 3-pole
		Cable	-
Light Technical		Temperature	
Luminous Flux	500 lm	Ambient temperature range	0 to +40 °C
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	83 lm/W	Controls and Dimming	
Color rendering index (CRI)	≥80	Dimmable	Yes
Light source color	830 warm white	Driver/power unit/transformer	Power supply unit regulating
Optic type	Symmetrical	Control interface	Analog
Luminaire light beam spread	36°	Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall length	55 mm
Overall width	55 mm
Overall height	55 mm
Overall diameter	75 mm
Dimensions (Height x Width x Depth)	55 x 55 x 55 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%
Product Data	
Order product name	RS060B LED5-36-/830 PSR II WH
Full product name	RS060B LED5-36-/830 PSR II WH
Full product code	871869607267799
Order code	910503910182
Material Nr. (12NC)	910503910182
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696072677
Numerator - Packs per outer box	24
EAN/UPC - Case	8718696072714

Dimensional drawing

