



# CoreLine panel

## RC132V LED34S/830 PSU W30L120 OC

CoreLine panel, 33 W, 1200x300 mm, 3400 lm, 3000 K, UGR19

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Panel range of LED products can be used to replace functional luminaires in general lighting applications. Both Non-Office Compliant (NOC) version and Office Compliant version (OC) are now available. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Product data

General Information		Glow-wire test	
Light source replaceable	No	EU RoHS compliant	Yes
Number of gear units	1 unit		
Driver included	Yes	Light Technical	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Luminous Flux	3,400 lm
Service tag	Yes	Correlated Color Temperature (Nom)	3000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	105 lm/W
Value ladder	Performance	Color rendering index (CRI)	≥80
CE mark	Yes	Beam angle of light source	120 degree(s)
Warranty period	5 years	Light source color	830 warm white
Flammability mark	For mounting on normally flammable surfaces	Optic type	-
ENEC mark	ENEC mark	Luminaire light beam spread	90°
		Unified glare rating CEN	19
		Operating and Electrical	
		Input Voltage	220-240 V
		Line Frequency	50 to 60 Hz
		Average CLO power consumption	33 W
		Inrush current	6 A

CoreLine panel

Inrush time	0.3 ms
Power Consumption	33 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	Cable 0.25 m with push-in connector 3-pole
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	White
Optical cover finish	Opal
Overall length	1,197 mm
Overall width	297 mm
Overall height	32 mm
Dimensions (Height x Width x Depth)	32 x 297 x 1197 mm

Approval and Application

Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
-------------------------	--

Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L75


Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data

Order product name	RC132V LED34S/830 PSU W30L120 OC
Full product name	RC132V LED34S/830 PSU W30L120 OC
Full product code	871869938103500
Order code	38103500
Material Nr. (12NC)	910503910315
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699381035
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699381035

Dimensional drawing



## CoreLine panel

