



Ledinaire SlimDownlight

DN065B LED10S/840 PSU II WH

Ledinaire SlimDownlight, 11 W, 1000 lm, 4000 K, Frosted, IP20

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need

Product data

General Information		Connection	
Light source replaceable	No	Screw connector	
Lighting Technology	LED	Temperature	
Value ladder	Value	Ambient temperature range	
Warranty period	3 years	0 to +35 °C	
Light Technical		Controls and Dimming	
Luminous Flux	1,000 lm	Dimmable	
Correlated Colour Temperature	4000 K	No	
Luminous efficacy (rated) (nom.)	91 lm/W	Driver/power unit/transformer	
Colour rendering index (CRI)	>80	Power supply unit (On/Off)	
Light source colour	840 neutral white	Mechanical and Housing	
Luminaire light beam spread	90° x 90°	Housing material	
Operating and Electrical		Plastic	
Line Frequency	50 or 60 Hz	Reflector material	
Input frequency	50 or 60 Hz	Polycarbonate	
Power Consumption	11 W	Optic material	
Power Factor (Fraction)	0.8	Polycarbonate	
		Fixation material	
		Stainless steel	
		Housing Colour	
		White	
		Optical cover/lens finish	
		Frosted	
		Overall length	
		30 mm	
		Overall width	
		30 mm	
		Overall height	
		30 mm	

Ledinaire SlimDownlight

Overall diameter	175 mm
Dimensions (height x width x depth)	30 x 30 x 30 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

Product Data	
Order product name	DN065B LED10S/840 PSU II WH
Full product name	DN065B LED10S/840 PSU II WH
Full EOC	871869938176999
Order code	38176999
Material no. (12 NC)	910503910332
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699381769
Numerator – packs per outer box	12
EAN/UPC – Case	8718699381806

Dimensional drawing

