



PowerBalance, surface mounted

SM461V LED28S/840 PSD W17L169 ACL

PowerBalance Surface-mounted, LED module, system flux 2800 lm, 840 neutral white, Power supply unit with DALI interface, ActiLume

When it comes to lighting an office space with LED luminaires, people are usually willing to invest in sustainability provided the investment pays back. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance is Philips' most energy-efficient office-norm-compliant LED luminaire. It more than halves energy costs compared to a T5 solution, and the light source has a longer lifetime. This results in significantly lower operational costs, ensuring a payback that meets the needs of the specification market. PowerBalance surface-mounted luminaires are easy to install on ceilings thanks to their intuitive mounting system. PowerBalance is also available in a recessed version.

Product data

General Information		
Lamp family code	LED28S [LED module, system flux 2800 lm]	
Cap-Base	- [-]	
Light source replaceable	No	
Number of gear units	1 unit	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Product family code	SM461V [PowerBalance Surface-mounted]	
Lighting Technology	LED	
Glow-wire test	Temperature 850 °C, duration 5 s	
Flammability mark	For mounting on normally flammable surfaces	
CE mark	Yes	
ENEC mark	ENEC plus mark	

PowerBalance, surface mounted

Warranty period	5 years
EU RoHS compliant	Yes
Embedded control	ActiLume

Light Technical

Luminous Flux	2,800 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	127 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	120°
Unified glare rating CEN	16

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	1 ms
Power Consumption	22 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Steel
------------------	-------

Reflector material	Polycarbonate
Optic material	-
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Matte
Overall length	1,685 mm
Overall width	171 mm
Overall height	85 mm
Dimensions (Height x Width x Depth)	85 x 171 x 1685 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	SM461V LED28S/840 PSD W17L169 ACL
Full product name	SM461V LED28S/840 PSD W17L169 ACL
Full product code	871794310322500
Order code	910504092303
Material Nr. (12NC)	910504092303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943103225
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943103225

PowerBalance, surface mounted

Dimensional drawing

