



SmartBalance Wall-mounted

WL484W LED46S/840 PSD IND WH

SmartBalance wall-mounted, LED Module, system flux 4600 lm, 840 neutral white, Power supply unit with DALI interface, White

Striking the right balance between the different lighting needs in a patient room is a challenge for many hospitals. That's why our bed-head luminaires offer some of the key functionalities required by both patients and staff. The SmartBalance, wall-mounted luminaire combines high-quality lighting performance with a stylish, timeless design. General ambience light is provided indirectly via the upper part of the luminaire. The lower part delivers direct, diffuse light, allowing patients to read and clinical staff to carry out examinations at the bed.

Product data

General Information			
Lamp family code	LED46S [LED Module, system flux 4600 lm]		useful life (B50) value also represents the B10 value.
Cap base	- [-]	Product family code	WL484W [SmartBalance wall-mounted]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	Embedded control	-
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC plus mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes

SmartBalance Wall-mounted

Light Technical	
Luminous Flux	4,600 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	124 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	- degree(s)
Light source colour	840 neutral white
Optic type	-
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	156°

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	0.18 ms
Power Consumption	37 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	20

Temperature	
Ambient temperature range	0 to +35 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing	
Housing material	Aluminium
Reflector material	Aluminium
Optic material	-

Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	White
Optical cover/lens finish	Textured
Overall length	900 mm
Overall width	152 mm
Overall height	52 mm
Dimensions (height x width x depth)	52 x 152 x 900 mm


Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data	
Order product name	WL484W LED46S/840 PSD IND WH
Full product name	WL484W LED46S/840 PSD IND WH
Full EOC	871794310528100
Order code	10528100
Material no. (12 NC)	910504094203
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8717943105281
Numerator – packs per outer box	1
EAN/UPC - Case	8717943105281

Dimensional drawing



SmartBalance Wall-mounted

