



SmartBalance Free Floor Standing

FS484F LED120S/830 PSD-T ACL CCH WH

SmartBalance FFS, LED module, system flux 12000 lm, 830 warm white, Power supply unit with DALI touch-switch and dimming interface, Micro-lens optic, ActiLume, Cable 3.0 m with Swiss plug 3-pole, White

Free floor-standing luminaires are loved by customers as the ideal solution for personally controlled, flexible and comfortable lighting. SmartBalance is the next step in free floor-standing luminaires. Thanks to the application of state-of-the-art LED technology, it offers not only increased energy efficiency, but also a compact and clean design that blends into any environment. SmartBalance is also available in recessed, surface-mounted and suspended versions.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If The above advice is not taken and The luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information			
Lamp family code	LED120S [LED module, system flux 12000 lm]	Gear	-
Cap-Base	- [-]	Driver included	Yes
Light source replaceable	No	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen
Number of gear units	2 units		

SmartBalance Free Floor Standing

	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	FS484F [SmartBalance FFS]
Lighting Technology	LED
Value ladder	Performance
Embedded control	ActiLume
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	12,000 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	132 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Light source color	830 warm white
Optic type	-
Optical cover type	Micro-lens optic
Luminaire light beam spread	114°
Unified glare rating CEN	13

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	50 A
Inrush time	2 ms
Power Consumption	91 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	Cable 3.0 m with Swiss plug 3-pole
Number of products on MCB of 16 A type B	10

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI touch-switch and dimming interface
Control interface	DALI

Constant light output	No
-----------------------	----

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Aluminum
Optic material	-
Optical cover material	Acrylate and polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	700 mm
Overall width	250 mm
Overall height	2,000 mm
Dimensions (Height x Width x Depth)	2000 x 250 x 700 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	FS484F LED120S/830 PSD-T ACL CCH WH
Full product name	FS484F LED120S/830 PSD-T ACL CCH WH
Full product code	871794311111400
Order code	910504095603
Material Nr. (12NC)	910504095603
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943111114
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943111114

SmartBalance Free Floor Standing

Dimensional drawing

