



SmartBalance Wall-mounted

WL484W LED40S/840 PSD D/I SW WH

SmartBalance wall-mounted, LED module, system flux 4000 lm, 840 neutral white, Power supply unit with DALI interface, White

Striking the right balance between the different lighting needs in a patient room is a challenge for many hospitals. That's why our bed-head luminaires offer some of the key functionalities required by both patients and staff. The SmartBalance, wall-mounted luminaire combines high-quality lighting performance with a stylish, timeless design. General ambience light is provided indirectly via the upper part of the luminaire. The lower part delivers direct, diffuse light, allowing patients to read and clinical staff to carry out examinations at the bed.

Product data

| General Information | | | |
|--------------------------|--|------------------------------------|---|
| Lamp family code | LED40S [LED module, system flux 4000 lm] | Product family code | WL484W [SmartBalance wall-mounted] |
| Cap-Base | - [-] | Lighting Technology | LED |
| Light source replaceable | No | Embedded control | - |
| Number of gear units | 2 units | CE mark | Yes |
| Gear | - | Warranty period | 5 years |
| Driver included | Yes | Flammability mark | For mounting on normally flammable surfaces |
| Remarks | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. | ENEC mark | ENEC plus mark |
| | | Glow-wire test | Temperature 650 °C, duration 5 s |
| | | EU RoHS compliant | Yes |
| | | Light Technical | |
| | | Luminous Flux | 4,000 lm |
| | | Correlated Color Temperature (Nom) | 4000 K |
| | | Luminous Efficacy (rated) (Nom) | 122 lm/W |

SmartBalance Wall-mounted

| | |
|-----------------------------|--------------------------|
| Color rendering index (CRI) | ≥80 |
| Number of light sources | 1 |
| Beam angle of light source | - degree(s) |
| Light source color | 840 neutral white |
| Optic type | - |
| Optical cover type | Polycarbonate bowl/cover |
| Luminaire light beam spread | 156° |

Operating and Electrical

| | |
|--|--------------------------|
| Input Voltage | 220-240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 48 A |
| Inrush time | 0.18 ms |
| Power Consumption | 32.7 W |
| Power Factor (Fraction) | 0.9 |
| Connection | Push-in connector 5-pole |
| Cable | - |
| Number of products on MCB of 16 A type B | 20 |

Temperature

| | |
|---------------------------|-------------|
| Ambient temperature range | 0 to +35 °C |
|---------------------------|-------------|


Controls and Dimming

| | |
|-------------------------------|---------------------------------------|
| Dimmable | Yes |
| Driver/power unit/transformer | Power supply unit with DALI interface |
| Control interface | DALI |
| Constant light output | No |

Mechanical and Housing

| | |
|------------------------|-----------------|
| Housing Material | Aluminum |
| Reflector material | Aluminum |
| Optic material | - |
| Optical cover material | Polycarbonate |
| Fixation material | Stainless steel |

Dimensional drawing



| | |
|-------------------------------------|-------------------|
| Housing Color | White |
| Optical cover finish | Textured |
| Overall length | 900 mm |
| Overall width | 152 mm |
| Overall height | 52 mm |
| Dimensions (Height x Width x Depth) | 52 x 152 x 900 mm |

Approval and Application

| | |
|------------------------------|-----------------------|
| Ingress protection code | IP40 [Wire-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Protection class IEC | Safety class I |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|----------------------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.38, 0.38) SDCM <3 |
| Power consumption tolerance | +/-10% |

Application Conditions

| | |
|------------------------------------|-------|
| Performance ambient temperature Tq | 25 °C |
| Maximum dim level | 1% |
| Suitable for random switching | No |

Product Data

| | |
|---------------------------------|---------------------------------|
| Order product name | WL484W LED40S/840 PSD D/I SW WH |
| Full product name | WL484W LED40S/840 PSD D/I SW WH |
| Full product code | 871869686902400 |
| Order code | 910504096303 |
| Material Nr. (12NC) | 910504096303 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696869024 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8718696869024 |

SmartBalance Wall-mounted

