



# TrueLine, surface mounted

## SM530C LED40S/840 PSD ACL PI5 L1170 ALU

TrueLine OC, LED module, system flux 4000 lm, 840 neutral white, Power supply unit with DALI interface, ActiLume, Push-in connector 5-pole, Aluminum

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated  $UGR < 19$ , which is compliant with all office norms (OC). TrueLine also comes in suspended and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

### Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

### Product data

## TrueLine, surface mounted

General Information	
Lamp family code	LED40S [LED module, system flux 4000 lm]
Cap-Base	- [-]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	SM530C [TrueLine OC]
Lighting Technology	LED
Value ladder	Specification
Embedded control	ActiLume
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	-
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	100°
Unified glare rating CEN	19
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	30 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	-
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	Aluminum
Optical cover finish	Frosted
Overall length	1,170 mm
Overall width	55 mm
Overall height	93 mm
Dimensions (Height x Width x Depth)	93 x 55 x 1170 mm
Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes
Product Data	
Order product name	SM530C LED40S/840 PSD ACL PI5 L1170 ALU
Full product name	SM530C LED40S/840 PSD ACL PI5 L1170 ALU
Full product code	871869687415800
Order code	910504098803
Material Nr. (12NC)	910504098803
Local order code	SM530C40LNWA

TrueLine, surface mounted

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696874158
Numerator - Packs per outer box	1

EAN/UPC - Case	8718696874158
----------------	---------------

Dimensional drawing

