



TrueLine, suspended

Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	4,750 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Light source color	840 neutral white
Optic type	-
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	100°
Unified glare rating CEN	16

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
End CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	34 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	Cable 1.7 m without plug 5-pole PVC silver
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-

Optic material	-
Optical cover material	Polymethyl methacrylate
Fixation material	Stainless steel
Housing Color	Aluminum
Optical cover finish	Frosted
Overall length	1,406 mm
Overall width	55 mm
Overall height	121 mm
Dimensions (Height x Width x Depth)	121 x 55 x 1406 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410
Full product name	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410
Full product code	871869687436300
Order code	87436300
Material Nr. (12NC)	910504100903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696874363
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696874363

TrueLine, suspended

Dimensional drawing

