



Impala TBS160

TBS160 4xTL-D18W HF C3 PI

IMPALA, 4, MASTER TL-D, 18 W, Electronic high-frequency, High-gloss mirror matt aluminum louver, Push-in connector 3-pole

Impala TBS160 is a functional recessed luminaire for 2, 3 or 4 TL-D fluorescent lamps. It offers a wide range of optics as well as a prismatic plate. The optics/plate are fitted to the housing by means of a clip for easy installation and maintenance. An external connection system enables the mains connection to be made without opening the luminaire. The luminaire fits in visible profile ceilings as standard and, using accessories, in concealed and plaster ceilings.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HF [Electronic high-frequency]
Product family code	TBS160 [IMPALA]
Embedded control	-
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 960 °C, duration 5 s
Light Technical	
Number of light sources	4
Light source color	-
Optic type	High-gloss mirror matt aluminum louver
Optical cover type	-

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	18 W
Connection	Push-in connector 3-pole
Cable	-
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TBS160 4xTL-D18W HF C3 PI

Impala TBS160

Full product name	TBS160 4xTL-D18W HF C3 PI
Full product code	872790059008100
Order code	910504402018
Material Nr. (12NC)	910504402018
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8727900590081
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900590081

Dimensional drawing

