



StyliD PerfectBeam

ST741T LED5S/930 PSR 7-43 BK

LED Module, system flux 500 lm - 930 warm white - Power supply unit regulating - Black

StyliD PerfectBeam has been developed specifically for museum applications. It strikes the perfect balance between presenting art and preserving it, between ever-changing exhibitions and the need for low maintenance and energy efficiency. The often conflicting demands for good visibility and conservation are now being met with LED lighting that emits no harmful UV or IR radiation. StyliD PerfectBeam presents works of art in their true colors, subtly attracting the viewer's eye, making it easy to see, interpret and appreciate masterpieces down to the smallest detail. It enables you to use light to evoke emotions and create an unforgettable museum experience. Its modular design, variable beam, beam shaping accessories and onboard dimming ensure maximum flexibility to cope with changing exhibitions and lighting needs, now and in the future.

Product data

General Information		Protection class IEC	Safety class II (II)
Lamp family code	LED5S [LED Module, system flux 500 lm]	Flammability mark	NO [-]
Light source colour	930 warm white	CE mark	CE mark
Light source replaceable	No	ENEC mark	-
Number of gear units	1 unit	Warranty period	5 years
Driver/power unit/transformer	PSR [Power supply unit regulating]	Outdoor optic type	-
Driver included	Yes	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Optical cover/lens type	PM [PMMA bowl/cover]		
Luminaire light beam spread	-		
Control interface	-		
Connection	No [-]		
Cable	-		

StyliD PerfectBeam

Constant light output	No
Number of products on MCB	-
LED engine type	LED
Light Technical	
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Operating and Electrical	
Input voltage	220/240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Power factor (min.)	-
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum
Reflector material	-
Optic material	Glass
Optical cover/lens material	Polymethyl methacrylate
Fixation material	-
Mounting device	No [-]
Optical cover/lens shape	-
Optical cover/lens finish	-
Overall length	258 mm
Overall width	91 mm
Overall height	248 mm
Overall diameter	91 mm
Colour	Black
Dimensions (height x width x depth)	248 x 91 x 258 mm (9.8 x 3.6 x 10.2 in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge protection (common/differential)	-

Initial Performance (IEC Compliant)


Initial luminous flux	684 lm
Luminous flux tolerance	+/-1%
Initial LED luminaire efficacy	32 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	90
Initial chromaticity	-
Initial input power	21 W
Power consumption tolerance	+/-2%

Application Conditions



Ambient temperature range	0 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	10%
Suitable for random switching	Not applicable

Product Data

Full product code	871829129778900
Order product name	ST741T LED55/930 PSR 7-43 BK
EAN/UPC – product	8718291297789
Order code	29778900
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910504801184
Net weight (piece)	1.300 kg





Photometric data



IFAS1_ST741T1xLED5593043+ST741ZLBSP



IFCC1_ST741T1xLED5593043+ST741ZLBSP

Photometric data





IFAS1_ST741T1xLED5S93024

IFCC1_ST741T1xLED5S93024



IFAS1_ST741T1xLED5S93024+ST741ZLBSP



IFCC1_ST741T1xLED5S93024+ST741ZLBSP



IFAS1_ST741T1xLED5S93024GF



IFCC1_ST741T1xLED5S93024GF

Photometric data





IFAS1_ST741T1xLED5S9307+ST741ZLBSP

IFCC1_ST741T1xLED5S9307+ST741ZLBSP



IFAS1_ST741T1xLED5S9307



IFCC1_ST741T1xLED5S9307



IFAS1_ST741T1xLED5S93043



IFCC1_ST741T1xLED5S93043

Photometric data



IFAS1_ST741T1xLED5S93043GF

IFCC1_ST741T1xLED5S93043GF



IFAS1_ST741T1xLED5S9307GF

IFCC1_ST741T1xLED5S9307GF

