



PerfectBeam gen.2

SHARP ZOOM DALI 930/BK/25W-IN220-240V

25 W, Power supply unit with DALI interface, Beam angle 7 to 55°, 54°

PerfectBeam gen2 has been dedicatedly designed the deliver excellent quality of light in museum applications. It strikes the perfect balance between presenting and preserving art, between ever-changing exhibitions and the need for low maintenance and energy efficiency. The often conflicting demands for good visibility and conservation are now satisfied with an LED lighting solution that doesn't emit any harmful UV or IR rays. PerfectBeam gen.2 presents masterpieces and objects in their true colors, subtly attracting the viewer's eye, making it easy to see, interpret and appreciate works of art down to the smallest detail. It enables you to use light to evoke emotions and create an unforgettable museum experience. Its modular design, variable beam, beam shaping accessories and onboard dimming or DALI ensure maximum flexibility to cope with changing exhibitions and lighting needs, now and in the future. PerfectBeam gen.2 is the right solution also in high-end fashion retail where you need to enhance colors, materials and underline details.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Lighting Technology	LED
CE mark	Yes
Warranty period	2 years
Flammability mark	-
ENEC mark	-
Glow-wire test	-

EU RoHS compliant	No
Light Technical	
Luminous Flux	1,560 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	62 lm/W
Color rendering index (CRI)	94
Beam angle of light source	120 degree(s)
Light source color	930 warm white
Optic type	Beam angle 7 to 55°

PerfectBeam gen.2

Luminaire light beam spread	54°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	18.6 W
Average CLO power consumption	25 W
Inrush current	0.851 A
Inrush time	1 ms
Power Consumption	25 W
Power Factor (Fraction)	0.97
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	90

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Glass
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Black
Optical cover finish	Frosted
Overall length	208 mm
Overall width	180 mm

Overall height	256 mm
Overall diameter	90 mm
Dimensions (Height x Width x Depth)	256 x 180 x 208 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	0.4338, 0.4030 (+/- 0.005); SDCM 2
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.01 %
-------------------------------	--------

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	3%
Suitable for random switching	No

Product Data

Order product name	SHARP ZOOM DALI 930/BK/25W-IN220-240V
Full product name	SHARP ZOOM DALI 930/BK/25W-IN220-240V
Full product code	871869919118400
Order code	910504801526
Material Nr. (12NC)	910504801526
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

PerfectBeam gen.2

