PHILIPS Lighting



High Power GearUnits

ECM330 MHN-LA1000W 220-480V ESI KIT

GearUnits, MASTER MHN-LA, 1000 W

Philips is one of the few companies able to provide total floodlight system solutions comprising all necessary elements - floodlight, lamp source and control gear unit. Our innovative high-power GearUnits are designed to meet our customers' need for a compact gear solution that is completely ready for installation. The pre-wired high-power control gear units are intended for use in combination with floodlights that are suitable for high-wattage HID lamps and cannot integrate electrical components because of limited space or high temperatures. A gear unit contains all electrical components (ballast, ignitors, capacitors), wiring and terminal blocks needed to ensure initial lamp ignition and proper operation of the lamp in stabilized current. The electromagnetic high-power GearUnits are available in both IP20 (ECB330) and IP65 (ECP330) versions. Within the GearUnits family there is also an electronic ballast version (ECM330) available in IP20, which is suitable for the MVF403 MHN-LA 1000 W and MVF404 MHN-SE HO 2000 W ArenaVision floodlights. The ArenaVision floodlight family is specially designed for TV broadcasts from indoor and outdoor sports facilities. Electronic-ballast GearUnits completely eliminate the flicker effect, thereby guaranteeing perfect images filmed with superslow-motion cameras.

Product data

MHN-LA [MASTER MHN-LA]
1 unit
EB [Electronic]
ECM330 [GearUnits]
Performance
Yes
_


ENEC mark	ENEC mark
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	220 to 480 V
Line Frequency	50 to 60 Hz

High Power GearUnits

Power Consumption	1,000 W
Connection	Screw connection block 3-pole
Temperature	
Ambient temperature range	-30 to +55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Material	Aluminum
Housing Color	Silver
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Mech. impact protection code	IK10 [20 J vandal-resistant]
Product Data	
Order product name	ECM330 MHN-LA1000W 220-480V ESI KIT
Full product name	ECM330 MHN-LA1000W 220-480V ESI KIT
Full product code	871869660105100
Order code	910505016324
Material Nr. (12NC)	910505016324
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696601051
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696601051

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 29 - data subject to change