



# SpeedStar

## BGP323 GRN195-/740 I DM SI T35

SpeedStar Large, LED GreenLine 19500 lm, Distribution medium, Flat glass

Municipalities are under pressure to meet energy conservation goals by reducing their energy consumption and carbon footprint while complying with lighting norms and standards. Our SpeedStar LED luminaire addresses these fundamental issues and provides a solution to reduce the impact on our environment. SpeedStar is an energy-efficient luminaire requiring minimal maintenance and incorporating the easy-to-upgrade LEDGINE, which can be connected to lighting regulation systems for further energy savings. This carbon-neutral luminaire is the ideal solution for functional road and street lighting.

### Product data

General Information			
Lamp family code	GRN195 [LED GreenLine 19500 lm]	Embedded control	-
Light source replaceable	Yes	CE mark	Yes
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Flammability mark	-
Photocell	-	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Light source engine type	LED	EU RoHS compliant	Yes
Product family code	BGP323 [SpeedStar Large]	Light Technical	
Lighting Technology	LED	Upward light output ratio	0.03
		Luminous Flux	20,500 lm
		Standard tilt angle posttop	5°
		Standard tilt angle side entry	0°
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	138 lm/W

Color rendering index (CRI)	70
Number of light sources	144
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	149 W
Power Factor (Fraction)	0.8
Connection	-
Cable	-
Number of products on MCB of 16 A type B	3

#### Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Mounting device	Universal for diameter 42 to 76 mm
Optical cover shape	Convex lens
Optical cover finish	Clear
Overall length	1,021 mm
Overall width	400 mm

Overall height	129 mm
Effective projected area	0.041 m²
Dimensions (Height x Width x Depth)	129 x 400 x 1021 mm
Parts color	All parts colored

#### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.370) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

#### Product Data

Order product name	BGP323 GRN195-/740 I DM SI T35
Full product name	BGP323 GRN195-/740 I DM SI T35
Full product code	871829134484100
Order code	34484100
Material Nr. (12NC)	910505016350
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291344841
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291344841

Dimensional drawing

