



# CitySoul gen2 LED Mini

**BPP530 LED35/740 I DM FG CO GR D9 T35**

CitySoul gen2 Mini, LED GreenLine 3500 lm, Distribution medium, Flat glass

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

## Product data

General Information		Lighting Technology	
Lamp family code	GRN35 [LED GreenLine 3500 lm]	Value ladder	Performance
Light source replaceable	Yes	Embedded control	-
Number of gear units	1 unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	Flammability mark	-
Light source engine type	LED	ENEC mark	ENEC mark
Product family code	BPP530 [CitySoul gen2 Mini]	EU RoHS compliant	Yes

# CitySoul gen2 LED Mini

<b>Light Technical</b>	
Upward light output ratio	0.03
Luminous Flux	2,940 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	131 lm/W
Color rendering index (CRI)	>70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium

<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	22.5 W
Power Factor (Fraction)	0.90
Connection	-
Cable	-
Number of products on MCB of 16 A type B	20

<b>Temperature</b>	
Ambient temperature range	-40 to +50 °C

<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

<b>Mechanical and Housing</b>	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 60 to 76 mm
Optical cover shape	Convex lens

Optical cover finish	Mask (anti-glare)
Overall length	629 mm
Overall width	538 mm
Overall height	94 mm
Effective projected area	0.024 m²
Dimensions (Height x Width x Depth)	94 x 538 x 629 mm
Parts color	Cover painted

<b>Approval and Application</b>	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class I

<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.370) SDCM<5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

<b>Over Time Performance (IEC Compliant)</b>	
Driver failure rate at 5000 h	0.15 %
Control gear failure rate at median useful life 100000 h	10 %

<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	50%

<b>Product Data</b>	
Order product name	BPP530 LED35/740 I DM FG CO GR D9 T35
Full product name	BPP530 LED35/740 I DM FG CO GR D9 T35
Full product code	871869661450100
Order code	61450100
Material Nr. (12NC)	910505016992
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696614501
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696614501

CitySoul gen2 LED Mini

Dimensional drawing

