



Maxos accessories

9MX056 EC7

ACC MAXOS

The swivel device is a versatile mechanical connecting device for Maxos TL-D and TL5 light-lines and enables variable angles between the light-lines. The minimum angle is 45 degrees. Due to its attractive design it is often used in application areas such as shops, schools and museums. Up to four light-lines can be connected with one swivel device. The housing is made of plastic, with a white or silver coating, and with inner supporting elements made of steel. If needed, the swivel device can accommodate lighting control sensors, loudspeakers, etc. It is pre-mounted with an adjustable quick hanger with a 1.25m steel suspension wire. One dedicated coupling piece (9MX056 CP-SD WH/SI) per trunking section is necessary to connect the trunking to the swivel device. Electrical components for mains feed-through have to be ordered as required.

Product data

General Information	
Accessory colour	-
Product family code	9MX056 [ACC MAXOS]
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Approval and Application	
Ingress protection code	-
Protection class IEC	Safety class I
Product Data	
Order product name	9MX056 EC7

Full product name	9MX056 EC7
Full EOC	403073213179200
Local code description	9MX056EC7
Order code	13179200
Material no. (12 NC)	910605019226
Local order code	9MX056EC7
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732131792
Numerator – packs per outer box	1
EAN/UPC - Case	4030732131792