



Maxos, mounting accessories

9MX056 MB WH

ACC MAXOS, 36 to 50°, White

The light line fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

Product data

| General Information | |
|-------------------------------------|--------------------|
| Angle | 36 to 50° |
| Accessory color | White |
| Product family code | 9MX056 [ACC MAXOS] |
| Mechanical and Housing | |
| Overall length | 30 mm |
| Overall width | 74 mm |
| Overall height | 45.3 mm |
| Dimensions (Height x Width x Depth) | 45 x 74 x 30 mm |
| Material | Steel |

| Approval and Application | |
|---------------------------------|-----------------|
| Ingress protection code | - |
| Protection class IEC | - |
| Product Data | |
| Order product name | 9MX056 MB WH |
| Full product name | 9MX056 MB WH |
| Full product code | 403073266188699 |
| Order code | 66188699 |
| Material Nr. (12NC) | 910605143826 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 4030732661886 |
| Numerator - Packs per outer box | 20 |

Maxos, mounting accessories

| | |
|----------------|---------------|
| EAN/UPC - Case | 4030732258666 |
|----------------|---------------|

