



Maxos, TL-D standard trunking

4MX056 581 5x2.5 WH

MAXOS TST8, White

The light line fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. All the light-line sections are made of hot-dip galvanized steel with a white or silver finish and available in lengths of 1, 2 and 3 electrical units 36 and 58 W. A flat ribbon cable (5 or 7 wires) or two flat ribbon cables (2 x 5 or 2 x 7 wires) are integrated in the light line and guarantee (in combination with an integrated phase selection switch and contact blocks) safe and correct cabling. The 7-wire cable is used to integrate light regulation or emergency lighting for those electrical units that are equipped with emergency battery packs. Double wiring (2 x 5 or 2 x 7 wires) is needed to provide a completely separate mains supply to the electrical units. Double wiring is mostly used for emergency lighting by central emergency batteries or separate switching. Hence, no extra contact blocks or wiring are required.

Product data

General Information	
Product family code	4MX056 [MAXOS TST8]
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Mechanical and Housing	
Housing Color	White
Overall length	1,530 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Product Data	
Order product name	4MX056 581 5x2.5 WH
Full product name	4MX056 581 5x2.5 WH
Full product code	403073257314199
Order code	910610017126

Maxos, TL-D standard trunking

Material Nr. (12NC)	910610017126
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732573141
Numerator - Packs per outer box	2

EAN/UPC - Case	4030732104680
----------------	---------------

Dimensional drawing

