



Maxos LED inserts for TTX400

4MX400 581 LED55S/840 PSD NB WH

Maxos LED Retrofit for TTX400 - 1 unit for TL-D 58 W - LED Module, system flux 5500 lm - 840 neutral white - Power supply unit with DALI interface - Narrow beam - White

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED inserts for TTX400 a truly future-proof solution.

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	LED55S [LED Module, system flux 5500 lm]
Beam angle of light source	120 °
Light source colour	840 neutral white
Cap base	- [-]
Light source replaceable	No
Number of gear units	1 unit
Gear	-

Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optic type	NB [Narrow beam]
Optical cover/lens type	PM [PMMA bowl/cover]
Luminaire light beam spread	50°
Emergency lighting	No [-]
Control interface	DALI
Connection	CU5 [Connection unit 5-pole]
Cable	-

Maxos LED inserts for TTX400

Protection class IEC	Safety class I (I)
Glow-wire test	650/30 [Temperature 650 °C, duration 30 s]
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	-
Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB	24
RoHS mark	RoHS mark
Product Family Code	4MX400 [Maxos LED Retrofit for TTX400]
Unified glare rating CEN	Not applicable

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	21 A
Inrush time	0.28 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Trunking length	581 [1 unit for TL-D 58 W]
Housing material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	1528 mm
Overall width	63 mm

Overall height	50 mm
Colour	White

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	5500 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	167 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Initial input power	33 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Ambient temperature range	-20 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	Not applicable

Product Data

Full product code	403073266255599
Order product name	4MX400 581 LED55S/840 PSD NB WH
EAN/UPC – product	4030732662555
Order code	66255599
Numerator – quantity per pack	1
Numerator – packs per outer box	3
Material no. (12NC)	910629124626
Net weight (piece)	1.895 kg




Maxos LED inserts for TTX400

Dimensional drawing




Maxos LED TTX400 retrofit 4MX400-433

Photometric data



IFGU_4MX400 G3 581 1xLED55S/840 PSD NB-General uniform lighting



IFPC_4MX400 G3 581 1xLED55S/840 PSD NB-Polar Indoor (combined)

