



# Maxos LED inserts for TTX400

## 4MX400 491 LED40S/840 PSD DA20 WH

Maxos LED Retrofit for TTX400, LED module, system flux 4000 lm, 840 neutral white, Power supply unit with DALI interface, Double asymmetric optic 20°, White

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required colour temperatures and glare factors. The minimalistic Maxos LED Industry 4MX400 panel inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED Industry 4MX400 panel inserts for TTX400 a truly future-proof solution.

### Product data

General Information		LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Lamp family code	LED40S [LED module, system flux 4000 lm]	Product family code	4MX400 [Maxos LED Retrofit for TTX400]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit		
Gear	-		
Driver included	Yes		
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of		

## Maxos LED inserts for TTX400

Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	4,000 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	166 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Double asymmetric optic 20°
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	20°
Unified Glare Rating (CEN)	Not applicable

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.28 ms
Power Consumption	24 W
Power Factor (Fraction)	0.97
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate

Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	1,474 mm
Overall width	63 mm
Overall height	50 mm
Dimensions (height x width x depth)	50 x 63 x 1474 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

### Product Data

Order product name	4MX400 491 LED40S/840 PSD DA20 WH
Full product name	4MX400 491 LED40S/840 PSD DA20 WH
Full EOC	403073266318799
Order code	66318799
Material no. (12 NC)	910629128326
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	4030732663187
Numerator – packs per outer box	3
EAN/UPC - Case	4030732260560

## Maxos LED inserts for TTX400

### Dimensional drawing

