



# Maxos LED Performer

## 4MX900 LED60S/840 PSD NB WH L1800

Maxos LED Performer, Generation 3, LED Module, system flux 6000 lm, 840 neutral white, Power supply unit with DALI interface, Narrow beam, White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

### Product data

General Information		Value ladder	
Lamp family code	LED60S [LED Module, system flux 6000 lm]	CE mark	Performance
Light source replaceable	No	Warranty period	Yes
Number of gear units	Unit	Flammability mark	5 years
Driver included	Yes	ENEC mark	-
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Product family code	4MX900 [Maxos LED Performer]	Glow-wire test	Temperature 650 °C, duration 30 s
Lighting Technology	LED	EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	6,000 lm
		Saturated Red (R9)	<50
		Correlated Colour Temperature	4000 K
		Luminous efficacy (rated) (nom.)	161 lm/W
		Colour rendering index (CRI)	≥80
		Number of light sources	1
		Beam angle of light source	120 degree(s)

# Maxos LED Performer

Light source colour	840 neutral white
Optic type	Narrow beam
Luminaire light beam spread	34°
Unified Glare Rating (CEN)	Not applicable

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.192 ms
Power Consumption	37.3 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	29

## Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	1,800 mm
Overall width	87 mm
Overall height	82 mm
Dimensions (height x width x depth)	82 x 87 x 1800 mm

## Approval and Application

Ingress protection code	IP40 [Wire-protected]
-------------------------	-----------------------

Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

## Product Data

Order product name	4MX900 LED60S/840 PSD NB WH L1800
Full product name	4MX900 LED60S/840 PSD NB WH L1800
Full EOC	403073266446799
Order code	66446799
Material no. (12 NC)	910629137426
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732664467
Numerator – packs per outer box	2
EAN/UPC - Case	4030732262281

# Maxos LED Performer

## Dimensional drawing

