



Maxos LED Performer

4MX900 LED90S/830 PSD WB WH L1800

Maxos LED Performer - LED module, system flux 9000 lm - 830 warm white - Power supply unit with DALI interface - Wide beam - White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Product data

General Information			
Number of light sources	1 pc	Glow-wire test	Temperature 650 °C, duration 30 s
Lamp family code	LED90S [LED module, system flux 9000 lm]	Flammability mark	For mounting on easily flammable surfaces
Beam angle of light source	120 °	CE mark	CE mark
Light source color	830 warm white	ENEC mark	ENEC mark
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Driver/power unit/transformer	Power supply unit with DALI interface	Constant light output	No
Driver included	Yes	Number of products on MCB of 16 A type B	18
Optic type	Wide beam	RoHS mark	RoHS mark
Luminaire light beam spread	90°		
Emergency lighting	-		
Control interface	DALI		
Connection	Connection unit 5-pole		
Cable	-		
Protection class IEC	Safety class I		

Maxos LED Performer

Product family code	4MX900 [Maxos LED Performer]
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	4.5 A
Inrush time	0.065 ms
Power Factor (Min)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Trunking length	-
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	1800 mm
Overall width	87 mm
Overall height	82 mm
Color	White

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	9000 lm
-------------------------------------	---------

Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	127 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	≥80
Initial chromaticity	(0.43, 0.40) SDCM <3.5
Initial input power	71 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80


Application Conditions

Ambient temperature range	-20 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable


Product Data

Full product code	403073266464199
Order product name	4MX900 LED90S/830 PSD WB WH L1800
EAN/UPC - Product	4030732664641
Order code	910629139226
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	910629139226
Net Weight (Piece)	2.900 kg

Dimensional drawing



Maxos LED Performer 4MX900-933



Maxos LED Performer 4MX900-933

Maxos LED Performer

