



Maxos LED Performer

4MX900 581 LED40S/840 PSU MB WH

Maxos LED Performer - Generation 3 - 1 unit for TL-D 58 W - LED Module, system flux 4000 lm - 840 neutral white - Power supply unit - Medium beam - White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Product data

General Information			
Number of light sources	1 [1 pc]	Flammability mark	D [For mounting on easily flammable surfaces]
Lamp family code	LED40S [LED Module, system flux 4000 lm]	CE mark	CE mark
Beam angle of light source	120 °	ENEC mark	ENEC mark
Light source colour	840 neutral white	Warranty period	5 years
Light source replaceable	No	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Number of gear units	1 unit	Constant light output	No
Driver/power unit/transformer	PSU [Power supply unit]	Number of products on MCB	24
Driver included	Yes	RoHS mark	RoHS mark
Optic type	MB [Medium beam]	Product Family Code	4MX900 [Maxos LED Performer]
Luminaire light beam spread	70°		
Emergency lighting	No [-]		
Connection	CU3 [Connection unit 3-pole]		
Cable	-		
Protection class IEC	Safety class I (I)		
Glow-wire test	650/30 [Temperature 650 °C, duration 30 s]		

Maxos LED Performer

Unified glare rating CEN	Not applicable
--------------------------	----------------

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	17.8 A
Inrush time	0.282 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Trunking length	581 [1 unit for TL-D 58 W]
Housing material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	1530 mm
Overall width	87 mm
Overall height	82 mm
Colour	White

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	4000 lm
-----------------------	---------

Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	133 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Initial input power	30 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80



Application Conditions

Ambient temperature range	-20 to +40 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data

Full product code	403073266477199
Order product name	4MX900 581 LED40S/840 PSU MB WH
EAN/UPC – product	4030732664771
Order code	66477199
Numerator – quantity per pack	1
Numerator – packs per outer box	2
Material no. (12NC)	910629140526
Net weight (piece)	2.500 kg

Dimensional drawing




Maxos LED Performer 4MX900-933

Maxos LED Performer 4MX900-933

Maxos LED Performer


Photometric data

4MX900 G3 581 1xLED40S/840 PSU MB
1 x 4000 lm



IFGU1_4MX900 G3 581 1xLED40S840 PSU MB.EPS

4MX900 G3 581 1xLED40S/840 PSU MB



IFPC1_4MX900 G3 581 1xLED40S840 PSU MB.EPS

