



Maxos LED Performer

4MX900 491 LED50S/840 PSU A30 WH

Maxos LED Performer, Generation 3, LED module, system flux 5000 lm, 840 neutral white, Power supply unit (On/Off), Asymmetrical mirror axis angle 30°, White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Product data

General Information			
Lamp family code	LED50S [LED module, system flux 5000 lm]	CE mark	Yes
Light source replaceable	No	Warranty period	5 years
Number of gear units	Unit	Flammability mark	-
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	Yes
Product family code	4MX900 [Maxos LED Performer]	Light Technical	
Lighting Technology	LED	Luminous Flux	5,000 lm
Value ladder	Performance	Saturated Red (R9)	<50
		Correlated Colour Temperature	4000 K
		Luminous efficacy (rated) (nom.)	155 lm/W
		Colour rendering index (CRI)	≥80
		Number of light sources	1
		Beam angle of light source	120 degree(s)
		Light source colour	840 neutral white

Maxos LED Performer

Optic type	Asymmetrical mirror axis angle 30°
Luminaire light beam spread	30°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	17.8 A
Inrush time	0.282 ms
Power Consumption	32.2 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	1,479 mm
Overall width	87 mm
Overall height	82 mm
Dimensions (height x width x depth)	82 x 87 x 1479 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
-------------------------	-----------------------

Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Not applicable

Product Data

Order product name	4MX900 491 LED50S/840 PSU A30 WH
Full product name	4MX900 491 LED50S/840 PSU A30 WH
Full EOC	403073266639399
Order code	66639399
Material no. (12 NC)	910629145926
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732666393
Numerator – packs per outer box	2
EAN/UPC - Case	4030732264568

Maxos LED Performer

Dimensional drawing

