



Maxos LED Performer

4MX900 491 LED75S/840 PSU A30 WH

Maxos LED Performer, Generation 3, LED Module, system flux 7500 lm, 840 neutral white, Power supply unit (On/Off), Asymmetrical mirror axis angle 30°, White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Product data

General Information		Value ladder		Performance	
Lamp family code	LED75S [LED Module, system flux 7500 lm]	CE mark		Yes	
Light source replaceable	No	Warranty period		5 years	
Number of gear units	1 unit	Flammability mark		-	
Driver included	Yes	ENEC mark		ENEC mark	
Remarks	*-Per Lighting Europe guidance paper	Glow-wire test		Temperature 650 °C, duration 30 s	
	“Evaluating performance of LED based luminaires - January 2018”: statistically	EU RoHS compliant		Yes	
	there is no relevant difference in lumen				
	maintenance between B50 and for				
	example B10. Therefore, the median useful				
	life (B50) value also represents the B10				
	value.				
Service tag	Yes				
Product family code	4MX900 [Maxos LED Performer]				
Lighting Technology	LED				
Light Technical					
		Luminous Flux		7,500 lm	
		Saturated Red (R9)		<50	
		Correlated Color Temperature (Nom)		4000 K	
		Luminous Efficacy (rated) (Nom)		149 lm/W	
		Color rendering index (CRI)		≥80	
		Number of light sources		1	
		Beam angle of light source		120 degree(s)	

Maxos LED Performer

Light source color	840 neutral white
Optic type	Asymmetrical mirror axis angle 30°
Luminaire light beam spread	30°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	17.8 A
Inrush time	0.282 ms
Power Consumption	50.2 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,479 mm
Overall width	87 mm
Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 87 x 1479 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
-------------------------	-----------------------

Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Not applicable

Product Data

Order product name	4MX900 491 LED75S/840 PSU A30 WH
Full product name	4MX900 491 LED75S/840 PSU A30 WH
Full product code	403073266711699
Order code	910629148526
Material Nr. (12NC)	910629148526
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732667116
Numerator - Packs per outer box	2
EAN/UPC - Case	4030732265596

Maxos LED Performer

Dimensional drawing

