



# Maxos LED

## 4MX850 491 LED55S/840 PSU WB SI

Maxos Led Industry, LED Module, system flux 5500 lm, 840 neutral white, Power supply unit (On/Off), Wide beam, Silver

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED Industry offers best-in-class energy savings while delivering high lux levels at the required colour temperatures and glare factors. The minimalistic Maxos LED Industry system comprises exchangeable mid-power LED boards mounted on a standard Maxos trunking rail. A choice of wide and medium-beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: the use of our upgradable LED engine platform makes Maxos LED Industry a truly future-proof solution.

### Product data

General Information		
Lamp family code	LED55S [LED Module, system flux 5500 lm]	useful life (B50) value also represents the B10 value.
Cap base	- [-]	Product family code
Light source replaceable	No	Lighting Technology
Number of gear units	Unit	Value ladder
Gear	-	CE mark
Driver included	Yes	Warranty period
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Flammability mark
		ENEC mark
		Glow-wire test
		EU RoHS compliant

# Maxos LED

Light Technical	
Luminous Flux	5,500 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	167 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Wide beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	90°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	17.8 A
Inrush time	0.282 ms
Power Consumption	33 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	-20 to +35 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Housing Colour	Silver

Optical cover/lens finish	Clear
Overall length	1,478 mm
Overall width	63 mm
Overall height	50 mm
Dimensions (height x width x depth)	50 x 63 x 1478 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data	
Order product name	4MX850 491 LED55S/840 PSU WB SI
Full product name	4MX850 491 LED55S/840 PSU WB SI
Full EOC	403073266531099
Order code	66531099
Material no. (12 NC)	910629151226
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732665310
Numerator – packs per outer box	3
EAN/UPC - Case	4030732263448

## Maxos LED

### Dimensional drawing

