



Maxos LED

4MX850 491 LED40S/840 PSU WB SI

Maxos Led Industry, LED module, system flux 4000 lm, 840 neutral white, Power supply unit (On/Off), Wide beam, Silver

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED Industry offers best-in-class energy savings while delivering high lux levels at the required colour temperatures and glare factors. The minimalistic Maxos LED Industry system comprises exchangeable mid-power LED boards mounted on a standard Maxos trunking rail. A choice of wide and medium-beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: the use of our upgradable LED engine platform makes Maxos LED Industry a truly future-proof solution.

Product data

General Information		
Lamp family code	LED40S [LED module, system flux 4000 lm]	useful life (B50) value also represents the B10 value.
Cap base	- [-]	Product family code
Light source replaceable	No	4MX850 [Maxos Led Industry]
Number of gear units	Unit	Lighting Technology
Gear	-	LED
Driver included	Yes	Value ladder
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Performance
		CE mark
		Yes
		Warranty period
		5 years
		Flammability mark
		-
		ENEC mark
		ENEC mark
		Glow-wire test
		Temperature 650 °C, duration 30 s
		EU RoHS compliant
		Yes

Maxos LED

Light Technical	
Luminous Flux	4,000 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	160 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Wide beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	90°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	17.8 A
Inrush time	0.282 ms
Power Consumption	25 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	-20 to +35 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel

Housing Colour	Silver
Optical cover/lens finish	Clear
Overall length	1,478 mm
Overall width	63 mm
Overall height	50 mm
Dimensions (height x width x depth)	50 x 63 x 1478 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data	
Order product name	4MX850 491 LED40S/840 PSU WB SI
Full product name	4MX850 491 LED40S/840 PSU WB SI
Full EOC	403073266547199
Order code	66547199
Material no. (12 NC)	910629152826
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732665471
Numerator – packs per outer box	3
EAN/UPC - Case	4030732263608

Maxos LED

Dimensional drawing

