



Maxos LED inserts for TTX400

4MX400 491 LED40S/840 PSU DA20 WH

Maxos LED Retrofit for TTX400, LED module, system flux 4000 lm, 840 neutral white, Power supply unit (On/Off), Double asymmetric optic 20°, White

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required colour temperatures and glare factors. The minimalistic Maxos LED Industry 4MX400 panel inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED Industry 4MX400 panel inserts for TTX400 a truly future-proof solution.

Product data

General Information	
Lamp family code	LED40S [LED module, system flux 4000 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	Yes

Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
---------	--

Maxos LED inserts for TTX400

Product family code	4MX400 [Maxos LED Retrofit for TTX400]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	4,000 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	160 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Double asymmetric optic 20°
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	20°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	17.8 A
Inrush time	0.282 ms
Power Consumption	25 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Steel
------------------	-------

Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	1,474 mm
Overall width	63 mm
Overall height	50 mm
Dimensions (height x width x depth)	50 x 63 x 1474 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data

Order product name	4MX400 491 LED40S/840 PSU DA20 WH
Full product name	4MX400 491 LED40S/840 PSU DA20 WH
Full EOC	403073266579299
Order code	66579299
Material no. (12 NC)	910629155826
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732665792
Numerator – packs per outer box	3
EAN/UPC - Case	4030732263943

Maxos LED inserts for TTX400

Dimensional drawing

