



Maxos LED Performer

4MX900 581 LED75S/840 PSD A30 WH

Maxos LED Performer, Generation 3, LED Module, system flux 7500 lm, 840 neutral white, Power supply unit with DALI interface, Asymmetrical mirror axis angle 30°, White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Product data

General Information		Value ladder		Performance		
Lamp family code	LED75S [LED Module, system flux 7500 lm]	CE mark	Yes			
Light source replaceable	No	Warranty period	5 years			
Number of gear units	1 unit	Flammability mark	-			
Driver included	Yes	ENEC mark	ENEC mark			
Remarks	*-Per Lighting Europe guidance paper	Glow-wire test	Temperature 650 °C, duration 30 s			
	“Evaluating performance of LED based luminaires - January 2018”: statistically	EU RoHS compliant	Yes			
	there is no relevant difference in lumen					
	maintenance between B50 and for					
	example B10. Therefore, the median useful					
	life (B50) value also represents the B10					
	value.					
Service tag	Yes					
Product family code	4MX900 [Maxos LED Performer]					
Lighting Technology	LED					

Light Technical	
Luminous Flux	7,500 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	149 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)

Maxos LED Performer

Light source color	840 neutral white
Optic type	Asymmetrical mirror axis angle 30°
Luminaire light beam spread	30°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.192 ms
Power Consumption	50.2 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	29

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,530 mm
Overall width	87 mm
Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 87 x 1530 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
-------------------------	-----------------------

Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

Product Data

Order product name	4MX900 581 LED75S/840 PSD A30 WH
Full product name	4MX900 581 LED75S/840 PSD A30 WH
Full product code	403073266811399
Order code	910629172426
Material Nr. (12NC)	910629172426
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732668113
Numerator - Packs per outer box	2
EAN/UPC - Case	4030732266814

Maxos LED Performer

Dimensional drawing

