



Maxos, projectors and HID solutions

9MX056 EP-F/TLD WH

ACC MAXOS, White

Accent lighting is part of the integral concept of Maxos. The light lines can be equipped with almost the full range of different projectors next to all the reflector solutions based on TL5 and TL-D fluorescent lamps. Often in specific areas of shops, projectors are requested in addition to fluorescent general lighting. 4MX094 units for projectors on conventional system. For Maxos trunkings with flat ribbon cable (5 x 2.5, 7 x 2.5) units with integrated 3C-rail are available. These units can be clicked into the trunking sections like a regular electrical unit. Projectors with 3C adapter can be fixed to the system. 4MX091 projector adapter for bus bar system. For Maxos bus bar trunking there are dedicated projector adapter units as well. These adapter units can be fixed to the trunking similar to a regular electrical unit. Maxos 4MX013 HID-lamp units. 4MX013 faceted reflector units with HID-lamps are often used to illuminate fruit and vegetables in supermarkets. The electrical components are integrated in a white-coated housing with the shape of a faceted reflector. The lengths of these units correspond to those of the 36 W light line. End plates for the beginning and the end of the light line are available as accessories.

Product data

General Information		Protection class IEC	
Accessory color	White	-	
Product family code	9MX056 [ACC MAXOS]	Product Data	
Approval and Application		Order product name	9MX056 EP-F/TLD WH
Ingress protection code	-	Full product name	9MX056 EP-F/TLD WH
		Full product code	403073210822000
		Order code	910683000526

Maxos, projectors and HID solutions

Material Nr. (12NC)	910683000526
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732108220
Numerator - Packs per outer box	1

EAN/UPC - Case	4030732108220
----------------	---------------

