



Maxos, mounting accessories

9MX056 BC L1800 WH

ACC MAXOS, White

The light line fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

Product data

| General Information | |
|--------------------------|--------------------|
| Accessory color | White |
| Product family code | 9MX056 [ACC MAXOS] |
| Approval and Application | |
| Ingress protection code | - |
| Protection class IEC | - |
| Product Data | |
| Order product name | 9MX056 BC L1800 WH |

| | |
|---------------------------------|--------------------|
| Full product name | 9MX056 BC L1800 WH |
| Full product code | 403073266607299 |
| Order code | 910683009526 |
| Material Nr. (12NC) | 910683009526 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 4030732666072 |
| Numerator - Packs per outer box | 30 |
| EAN/UPC - Case | 4030732264247 |