



# EFix TCS260

## ZCS260 SMT-L1500 SI

### EFix TCS260, Accessory

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

### Product data

| General Information |                           |
|---------------------|---------------------------|
| Accessory color     | Silver                    |
| Product family code | ZCS260 [EFix accessories] |
| Value ladder        | Performance               |
| Product Data        |                           |
| Order product name  | ZCS260 SMT-L1500 SI       |
| Full product name   | ZCS260 SMT-L1500 SI       |
| Full product code   | 872790062212600           |

|                                 |               |
|---------------------------------|---------------|
| Order code                      | 62212600      |
| Material Nr. (12NC)             | 910925229811  |
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8727900622126 |
| Numerator - Packs per outer box | 1             |
| EAN/UPC - Case                  | 8727900622126 |