




High Power GearUnits

ECB330 MHN-SA2000W 380-430V FU

GearUnits, MASTER MHN-SA, 2000 W

Philips is one of the few companies able to provide total floodlight system solutions comprising all necessary elements – floodlight, lamp source and control gear unit. Our innovative high-power GearUnits are designed to meet our customers' need for a compact gear solution that is completely ready for installation. The pre-wired high-power control gear units are intended for use in combination with floodlights that are suitable for high-wattage HID lamps and cannot integrate electrical components because of limited space or high temperatures. A gear unit contains all electrical components (ballast, ignitors, capacitors), wiring and terminal blocks needed to ensure initial lamp ignition and proper operation of the lamp in stabilized current. The electromagnetic high-power GearUnits are available in both IP20 (ECB330) and IP65 (ECP330) versions. Within the GearUnits family there is also an electronic flicker-free ballast version (ECM330) available in IP20, which is suitable for the MVF403 MHN-LA 1000 W and MVF404 MHN-SE HO 2000 W ArenaVision floodlights. The ArenaVision floodlight family is specially designed for TV broadcasts from indoor and outdoor sports facilities. Electronic-ballast GearUnits completely eliminate the flicker effect, thereby guaranteeing perfect images filmed with super-slow-motion cameras.

Product data

General Information		Value ladder	Performance
Lamp family code	MHN-SA [MASTER MHN-SA]		
Number of gear units	1 unit		
Gear	EB [Electronic]		
Product family code	ECB330 [GearUnits]		
Flammability mark	For mounting on normally flammable surfaces		
CE mark	Yes		
ENEC mark	ENEC mark		
Light Technical			
Number of light sources		1	
Operating and Electrical			
Input Voltage		380 to 430 V	
Line Frequency		50 to 60 Hz	

High Power GearUnits

Power Consumption	2,000 W
Connection	Screw connection block 3-pole
Temperature	
Ambient temperature range	-30 to +55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Silver
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK10 [20 J vandal-resistant]

Energy Efficiency Index	A2
Product Data	
Order product name	ECB330 MHN-SA2000W 380-430V FU
Full product name	ECB330 MHN-SA2000W 380-430V FU
Full product code	871829106882200
Order code	910925258212
Material Nr. (12NC)	910925258212
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291068822
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291068822

Dimensional drawing

