



Pacific Performer

WT360C 2xTL5-54W/830 HFP WR

Pacific Performer, 2, TL5, 54 W, 830 warm white, HF Performer, White reflector without louver

If you want to reduce your energy costs and join a growing number of companies doing their part for sustainability, then the Pacific Performer WT360C is for you. Featuring a fresh new design, this waterproof luminaire combines highly energy-efficient T5 lamp technology with a new reflector system offering excellent beam control. What's more, installation is quick and easy, thanks to the flexible ceiling brackets and smart end-caps. And because the light engine itself can be replaced, it will be possible to upgrade to LEDs in the future without having to change the entire luminaire.

Product data


General Information		Operating and Electrical	
Lamp family code	TL5 [TL5]	Power Consumption	54 W
Gear	HFP [HF Performer]	Connection	-
Product family code	WT360C [Pacific Performer]	Mechanical and Housing	
CE mark	Yes	Fixation point length distance (Nom)	900 mm
Flammability mark	For mounting on normally flammable surfaces	Overall length	1,321 mm
ENEC mark	ENEC mark	Approval and Application	
Glow-wire test	Temperature 850 °C, duration 5 s	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light Technical		Mech. impact protection code	IK08 [5 J vandal-protected]
Number of light sources	2	Protection class IEC	Safety class I
Light source color	830 warm white		
Optic type	White reflector without louver		

Pacific Performer

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	WT360C 2xTL5-54W/830 HFP WR
Full product name	WT360C 2xTL5-54W/830 HFP WR
Full product code	871829103058400
Order code	910925305812

Material Nr. (12NC)	910925305812
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291030584
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291030584

Dimensional drawing



Product	A	B	B	B	C
WT360C 2xTL5-54W/830 HFP WR	1,300 mm	850 mm	900 mm	950 mm	1,321 mm

