



Cabana2 BY150P

BY150P 1xHPI-P400W-BU K IC SGR IP65

Cabana 2 - 1 pc - MASTER HPI Plus - 400 W - Base-Up (BU) - Lamp(s) included - Inductive parallel compensated - SON gear - Dust penetration-protected, jet-proof

Cabana 2 is a functional high-bay indoor luminaire for high-intensity discharge lamps. It is supplied with a reflector, which can be attached to the unit without screws by means of an ingenious bayonet construction. The innovative external beam regulator enables easy lamp adjustment (narrow or wide beam) at the installation site. The external connector means the electrical connection can be made without opening the unit. Two versions are available: the standard version for SON and HPI-P lamps, and a round version for CDM-TMW lamps.

Product data

General Information		Operating and Electrical	
Number of light sources	1 [1 pc]	Protection class IEC	Safety class I (I)
Lamp family code	HPI-P [MASTER HPI Plus]	Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Lamp power	400 W	Flammability mark	F [For mounting on normally flammable surfaces]
Light source colour	645 neutral white	Lamp position	NO [-]
Lamp system description	Base-Up (BU)	CE mark	CE mark
Cap base	E40 [E40]	ENEC mark	-
Auxiliary light source	No [-]	Suspension accessories	No [-]
Kombipack	Lamp(s) included	Product Family Code	BY150P [Cabana 2]
Light source replaceable	Yes		
Compensation circuit	Inductive parallel compensated	Input voltage	230 V (default) or 240 V
Gear	SGR [SON gear]	Input frequency	50 Hz
Driver included	Yes	Ignitor	SKD [Digital semi-parallel MK4]
Emergency lighting	No [-]		
Connection	PI [Push-in connector 3-pole]		

Cabana2 BY150P

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminum
Reflector material	Aluminum
Optical cover/lens material	Glass
Colour	Black

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Init. Corr. colour temperature	4500 K
--------------------------------	--------

Application Conditions


Ambient temperature range	-15 to +35 °C
Suitable for random switching	Not applicable

Product Data

Full product code	871829190572100
Order product name	BY150P 1xHPI-P400W-BU K IC SGR IP65
EAN/UPC – product	8718291905721
Order code	90572100
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910925438246
Net weight (piece)	11.600 kg



Dimensional drawing



Cabana2 BY150P

