



OptiFlood LED BVP506

BVP506 ECO166-3S/657 I A GR T35

OptiFlood LED, LED EconomyLine 16600 lm, Asymmetrical

OptiFlood LED is a range of stylish, extremely efficient asymmetric floodlights that can be used to illuminate large areas. Designed around the latest LED technology, it offers significant energy and maintenance savings compared with conventional HID systems. Thanks to its highly efficient LEDGine area optics, it can be used for area lighting applications that have traditionally required HID-equivalent power levels. Integrated controls are available as an option, enabling additional energy savings. And LED upgrades can be easily incorporated, making this a truly future-proof solution. With its compact shape and aesthetically pleasing design, OptiFlood LED can be used in applications where design and appearance are just important as technical performance.

Product data

General Information			
Lamp family code	ECO166 [LED EconomyLine 16600 lm]		life (B50) value also represents the B10 value.
Light source replaceable	Yes	Light source engine type	LED
Number of gear units	1 unit	Product family code	BVP506 [OptiFlood LED]
Driver included	Yes	Lighting Technology	LED
Photocell	-	Flammability mark	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful	CE mark	Yes
		ENEC mark	ENEC mark
		Warranty period	5 years
		EU RoHS compliant	Yes
		Embedded control	-

OptiFlood LED BVP506

Light Technical	
Upward light output ratio	0
Luminous Flux	14,380 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	99 lm/W
Color rendering index (CRI)	70
Number of light sources	64
Light source color	757 cool white
Optical cover type	Clear glass
Luminaire light beam spread	48° x 66°
Optic type outdoor	Asymmetrical

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	[delete] W
End CLO power consumption	[delete] W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	140 W
Power Factor (Fraction)	0.9
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	8

Temperature	
Ambient temperature range	-30 to +35 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	-

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	730 mm
Overall width	460 mm
Overall height	176 mm
Effective projected area	0.1 m²
Dimensions (Height x Width x Depth)	176 x 460 x 730 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	4/4 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.33, 0.34) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data	
Order product name	BVP506 ECO166-3S/657 I A GR T35
Full product name	BVP506 ECO166-3S/657 I A GR T35
Full product code	871829141785900
Order code	910925439360
Material Nr. (12NC)	910925439360
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291417859
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291417859

OptiFlood LED BVP506

Dimensional drawing

